



GIVRO PR SET



GIVRO-90L



GIVRO-I




GIVRO PR SET



GIVRO-T



GIVRO-X



GIVRO-90L

GIVRO-I




GIVRO-PEND

x10




GIVRO-Z

x3



GIVRO-T

GIVRO-X



GIVRO-PEND



GIVRO-Z

► tworzywo sztuczne

► plastic

Kanlux	Kanlux			[g]
GIVRO PR SET	08637	przewód przyłączeniowy / connecting cord	1/-/75	167
GIVRO-90L	08636	łącznik 90° / connector 90°	1/-/300	8
GIVRO-I	08639	łącznik "I" / connector "I"	1/-/700	4
GIVRO-T	08641	łącznik "T" / connector "T"	1/-/300	12
GIVRO-X	08635	łącznik "X" / connector "X"	1/-/300	14
GIVRO-PEND	08640	zawieszka / suspension	1/-/250	13
GIVRO-Z	08638	zaślepka / stopper	1/-/500	5



GIVRO PR SET zasilany 220-240V~; 50/60Hz, służy do podłączenia zasilania do węża / GIVRO-90L służy do połączenia dwóch odcinków węża pod kątem 90° / GIVRO-I służy do połączenia liniowego dwóch odcinków węża / GIVRO-T służy do połączenia na kształt litery „T” trzech odcinków węża / GIVRO-X służy do połączenia na kształt litery „X” czterech odcinków węża / GIVRO-PEND służy do mocowania węża na powierzchni montażowej; opakowanie zawierające 10 sztuk / GIVRO-Z służy do zaślepienia wolnych końców węża; opakowanie zawierające 3 sztuki

GIVRO PR SET: powered 220-240V~; 50/60Hz is used to connect power supply to the LED rope / GIVRO-90L is used to connect two sections of LED rope at an angle of 90° / GIVRO-I used to connect two sections of LED rope linearly / GIVRO-T is used to connect three sections of LED rope to form a „T” shape / GIVRO-X is used to connect three sections of LED rope to form an „X” shape / GIVRO-PEND is used to attach the LED rope to a mounting surface; pack of 10 pieces / GIVRO-Z is used to close the free ends of the LED rope, pack of 3 pieces